


SKIMZ ZAR | SPECIFICATIONS

Model	Dimensions (mm)	DC Pump	Pump (Watt)	Zeolite Media	2 Preset Mode	For Aquarium (Litre)
ZAR127	155 x 170 x 475	QP5.0	max. 30W	up to 1.2L	Twice/day or hourly	up to 480
ZAR157	185 x 200 x 540	QP7.0	max. 60W	up to 3.5L	Twice/day or hourly	up to 1,400



Zeolite Auto Reactor

SKIMZ SINGAPORE

5 Ang Mo Kio Ind. Park 2A
04-30 AMK Tech II
Singapore 567760

info@skimz.sg | +65 6250 1501

www.skimz.sg



1



2



4



5

Skimz Zeolite Auto Reactor (ZAR) is the simple approach which allow you to have a more active influence over the water chemistry, which is vital to the growth and colouration of corals, especially SPS corals.

Zeolite-based probiotic reactor is becoming a popular form of filtration over recent years. By utilizing the nutrient processing traits of selective bacteria strains as well as a substrate facilitative to their metabolic needs, Zeolite-based probiotic reactor effectively creates Ultra Low Nutrient (ULN) conditions that most closely mimic reef environments.

Probiotic methods require a good protein skimmer for effective use.

The New **Skimz Zeolite Auto Reactor (ZAR)** features:

- 2 preset auto flushing modes
- 4 preset flow rates
- Pause for dosing bacteria
- Double-Speed Button



3

1. Keyhole slot for quick attachment and detachment.
2. Easy access to the reactor pump.
3. Access Port for dosing bacteria.

4. ZeoAuto™ Controller.
5. Changing of media is made easy with the split body design.
6. Skimz QuietPro DC pump.

Skimz ZAR Zeolite Reactor consists of 4 preset flow rates for different volume of zeolite media:

- **ZAR127** - 0.3, 0.6, 0.9 and 1.2L
- **ZAR157** - 0.9, 1.8, 2.7 and 3.5L

Hobbyists can select the desired flow rate according to the amount of media they use and with a press of a button the flow rates can be double up for faster absorption of unwanted nutrient.

Hobbyists can also choose either of the 2 pre-set flushing modes when operating the reactor. Each mode has different characteristic which is in line with the old twice a day and new automated hourly flushing method.

- **Mode 1:** Twice a day flushing
- **Mode 2:** Auto hourly flushing

The New **Zeolite Auto Reactor** can fulfill the needs of both old school and new users. Hobbyists will not have to worry about forgetting the twice daily pushing-pulling the PVC rode.



6